

Working Smarter with Less Splicing/Jumpers and Fewer Modules

“SloanStretch” and “Snap and Stretch” features are the key

ChanneLED 5 - SloanStretch



Simply pull the modules apart

SloanStretch feature extends the wire (+2”) between modules when needed.

ChanneLED 5 available in - red, white and warm white

Great White 3 - Snap and Stretch



Just Snap apart and Stretch

Snap and Stretch feature allows you to create two functional modules for maximum flexibility.



12” wide letter with only 2 rows

Use the SloanStretch to line up your next row, thus using fewer module.



Use a whole or a half module

The Snap and Stretch feature also provides the flexibility of using only half a module.



No splicing or jumpers needed

SloanStretch makes it easier to go around a corner or go over conduit without splicing or jumpers.



Use both for more flexibility

Great White 3 has both the Snap and Stretch and the SloanStretch features. In addition to being able to create two half modules you can also stretch the wire an additional 3” between whole modules for added flexibility.